



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-6 @20°C	1.10 ohms ±10%
INDUCTANCE	1-6 10kHz, 100mVAC, Ls	1.20mH ±10%
SATURATION CURRENT	20% rolloff from initial	200mA



Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-0847 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.001 [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750311907
6B	5/20			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750311907	SPECIFICATION SHEET 1 OF 1
6A	11/10	SEE REVISION SHEET FOR REVISION LEVEL				