




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

- D.C. RESISTANCE (@20°C): 3-1, 2.250 Ohms ±10%.
 5-6, 0.080 Ohms max.
 4-5, 0.150 Ohms max.
- DIELECTRIC RATING: 1000VAC, 1 minute tested by applying 1250VAC for 1 second between pins 3-4.
- INDUCTANCE: 2.54 mH ±10%, 20kHz, 100mVAC, 0mADC, 3-1, Ls.
- LEAKAGE INDUCTANCE: 20.0µH max., 100kHz, 100mVAC, 3-1(4+5+6), Ls.
- TURNS RATIO: (3-1):(4-6), (8.36):(1.00), ±1%.
 (3-1):(4-5), (13.14):(1.00), ±1%.

OPERATING TEMPERATURE RANGE: -40°C to 85°C including temp. rise.

WE-Midcom, Inc. Watertown, SD USA Toll Free: 800-643-2661 Fax: 605-886-4486	Unless otherwise specified, tolerances are as follows: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 (.127mm)		WE-Midcom, Inc.	
	Drawing Title Transformer		Drawing Number 750312145	Rev. 00
This drawing is dual dimensioned. Dimensions in brackets are in millimeters	Revisions: See Sheet 1		Scale ----	Sheet 2 of 5
Engineer:TST			02/09/2011	