


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-5 @20°C	1.35 ohms ±10%
D.C. RESISTANCE	9-11 @20°C	0.105 ohms ±10%
INDUCTANCE	2-5 10kHz, 100mVAC, Ls	1.10mH ±10%
SATURATION CURRENT	20% rolloff from initial	4.0A
LEAKAGE INDUCTANCE	2-5 tie(9+11), 100kHz, 100mVAC, Ls	465uH typ.
DIELECTRIC	5-9 1875VAC, 1 second	1500VAC, 1 minute
URNS RATIO	(5-2):(9-11)	57:1, ±3%

GENERAL SPECIFICATIONS:
 OPERATING TEMPERATURE RANGE: -40°C to +125°C.

Wire insulation & RoHS status not affected by wire color.
 Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64	Decimals: ±.005 [.13] Footprint: ±.001 [.03]	DRAWING TITLE	PART NO.
		Method: Tray PKG-0622 www.we-online.com/midcom				INDUCTOR	750312407
6A	6/11	SEE REVISION SHEET FOR	REVISION LEVEL	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		eiSos p/n: 750312407	SPECIFICATION SHEET 1 OF 1

