





CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



TERM. NO.'s FOR REF. ONLY



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

D.C. RESISTANCE (@20°C):	3-1 , 0.680 Ohms ±10%. 5-4 , 0.220 Ohms ±10%. 2-1 , 0.300 Ohms ±10%.
DIELECTRIC RATING:	500VAC, 1 minute tested by applying 625VAC for 1 second between pins 3-5.
INDUCTANCE:	1.06 mH ±10%, 100kHz, 100mVAC, 0mADC, 3-1, Ls.
URNS RATIO:	(3-1):(2-1) , (2.50):(1.00), ±1%. (3-1):(5-4) , (6.18):(1.00), ±1%.

Safety Standard Undefined

OPERATING TEMPERATURE RANGE: -40°C to 125°C including temp. rise.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

WE-Midcom, Inc. Watertown, SD USA Toll Free: 800-643-2661 Fax: 605-886-4486	Unless otherwise specified, tolerances are as follows: Angles: ±1° Fractions: ±1/64 Decimals: ±.005(.127mm)		WE-Midcom, Inc.	
	Drawing Title <h1>Transformer</h1>		Drawing Number <h2>750312511</h2>	Rev. 00
Revisions: See Sheet 1		Scale ----	Sheet 2 of 5	
Engineer:TST			07/14/2011	

This drawing is dual dimensioned.
Dimensions in brackets are in millimeters