




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes




ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-4 @20°C	0.068 ohms max.
D.C. RESISTANCE	3-5 @20°C	0.060 ohms max.
INDUCTANCE	3-5 10kHz, 310mVAC, Ls	200uH ±10%
SATURATION CURRENT	3-5 20% rolloff from initial	8.8A
SELF RESONANT FREQUENCY		1.8MHz min.
DIELECTRIC	2-5 1250VAC, 1 second	1000VAC, 1 minute
URNS RATIO	(5-3):(2-4)	10:1, ±1%



Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Fractions: $\pm 1/64$	Decimals: $\pm .005$ [.13] Footprint: $\pm .001$ [.03]	DRAWING TITLE	PART NO.
		Method: Tray PKG-0825 www.we-online.com/midcom		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		INDUCTOR	750312943
6A	5/16	SEE REVISION SHEET FOR REVISION LEVEL		eiSos p/n: 750312943			SPECIFICATION SHEET 1 OF 1