




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	7.55 ohms $\pm 10\%$
D.C. RESISTANCE	3-5 @20°C	1.00 ohms $\pm 10\%$
D.C. RESISTANCE	4-5 @20°C	0.600 ohms $\pm 10\%$
D.C. RESISTANCE	FL1-FL2 @20°C	0.100 ohms max.
INDUCTANCE	1-2 10kHz, 100mVAC, Ls	1.85mH $\pm 10\%$
SATURATION CURRENT	1-2 20% rolloff from initial	360mA
LEAKAGE INDUCTANCE	1-2 tie(FL1+FL2, 3+4+5), 100kHz, 100mVAC, Ls	75uH typ., 110uH max.
DIELECTRIC	1-FL1 tie(2+5), 3750VAC, 1 second	3000VAC, 1 minute
DIELECTRIC	1-5 1250VAC, 1 second	1000VAC, 1 minute
TURNS RATIO	(1-2):(FL1-FL2)	15:1, $\pm 1\%$
TURNS RATIO	(1-2):(5-3)	6.875:1, $\pm 1\%$
TURNS RATIO	(1-2):(5-4)	16.5:1, $\pm 1\%$

GENERAL SPECIFICATIONS:
Safety standard undefined.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-1219 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Fractions: $\pm 1/64$	Decimals: $\pm .005$ $[\.13]$ Footprint: $\pm .001$ $[\.03]$	DRAWING TITLE TRANSFORMER	PART NO. 750313567
6A	12/19	SEE REVISION SHEET FOR REVISION LEVEL	REVISION LEVEL	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		eiSos p/n: 750313567	compliant RoHS SPECIFICATION SHEET 1 OF 1