




SOLDER SUFFIX	CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE	(6F)
	Sn63%, Pb37%	No	No	
LF1	Sn96%, Ag4%	Yes	Yes	



**ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:**

- D.C. RESISTANCE (@20°C): 3-1, 0.275 ohms max.  
4-6, 2.700 ohms max.
- DIELECTRIC RATING: 500VDC for 1 second between PRI-SEC.
- INDUCTANCE: 230uH min., 10kHz, 100mVAC, 3-2, Ls.
- URNS RATIO: (4-5):(3-2) = 4:1, ±1%.  
(5-6):(3-2) = 4:1, ±1%.  
(5-6):(2-1) = 4:1, ±1%.

(6D) OPERATING TEMPERATURE RANGE: -40°C to +85°C.

Midcom p/n 30802R-LF1 is eiSos p/n: 750030802.

DETAILS SUBJECT TO CHANGE

Unless otherwise specified: Tolerances: Angles: ±1° Fractions: ±1/64 Decimals: ±.005[.13]	DRAWING TITLE <h2 style="text-align: center;">TRANSFORMER</h2>		PART # 30802R/-LF1
	eiSos p/n: 750030802		
This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	SEE REVISION SHEET FOR REVISION LEVEL	SPECIFICATION SHEET 1 OF 1	