



SOLDER SUFFIX	CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE	(6D)
	Sn63%, Pb37%	No	No	
LF1	Sn96%, Ag4%	Yes	Yes	



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:


D.C. RESISTANCE (@20°C): 3-4, 0.210 ohms max.
1-6, 0.210 ohms max.

DIELECTRIC RATING: 400VDC, 1 minute tested by applying 500VDC for 1 second between 1-3.

(6B) INDUCTANCE: 33uH ±10%, 100kHz, 100mVAC, 0/1.5ADC, 3-4, Ls.

TURNS RATIO: (1-6):(3-4) = 1:1, ±1%.

DETAILS SUBJECT TO CHANGE

Unless otherwise specified: Tolerances: Angles: ±1° Fractions: ±1/64 Decimals: ±.005[.13]	DRAWING TITLE <h2 style="text-align: center;">INDUCTOR</h2>	 www.midcom-inc.com	PART NO. <h2 style="text-align: center;">30945R/-LF1</h2>	REV. 6D 7/06	PART # 30945R/-LF1
	eiSos p/n: SEE REVISION SHEET FOR REVISION LEVEL				