


SOLDER SUFFIX	CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE	6F 6G
LF1	Sn96%, Ag4%	Yes	Yes	



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

- D.C. RESISTANCE (@20°C): 1-2, 0.35 ohms max.
3-4, 0.35 ohms max.
- DIELECTRIC RATING: 3000VAC, 1 minute tested by applying 3750VAC for 1 second between 1-4.
- INDUCTANCE: 450uH min., 10kHz, 100mVAC, 1-2, Ls.
- TURNS RATIO: (4-3):(1-2) = 1:1, ±1%.

- 6C Designed to comply with the following requirements as defined by IEC60950-1, EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:
- Supplementary insulation for a primary circuit at a working voltage of 250Vrms.
- 6G Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

6C 6H	
AGENCY NUMBER	
UL 60950-1	E205930
CSA 60950-1 (Via CUL)	E205930
IEC 60950-1 (Via CB cert.)	US/8440/UL
JAPAN (Via CB cert.)	US/8440/UL
ACA/AUSTEL (Via CB cert.)	US/8440/UL

Unless otherwise specified: Tolerances: Angles: ±1° Fractions: ±1/64 Decimals: ±.005[.13]	DRAWING TITLE <h3>TRANSFORMER</h3>		PART NO. 6G REV. 6H 82157R-LF1 10/17	PART# 82157R-LF1
	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.			