

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect




ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER		TEST CONDITIONS	VALUE
D.C. RESISTANCE	3-2	@20°C	4.95 ohms ±10%
D.C. RESISTANCE	7-6	@20°C	0.080 ohms ±10%
D.C. RESISTANCE	4-1	@20°C	1.64 ohms ±10%
INDUCTANCE	3-2	10kHz, 100mVAC, Ls	2.50mH ±10%
SATURATION CURRENT		20% rolloff from initial	135mA
LEAKAGE INDUCTANCE	3-2	tie(1+4, 6+7), 100kHz, 100mVAC, Ls	44uH typ., 66uH max.
DIELECTRIC	1-7	tie(1+2), 2000VAC, 1 second	-
DIELECTRIC	1-2	625VAC, 1 second	-
URNS RATIO		(4-1):(7-6)	3:1, ±1%
URNS RATIO		(3-2):(4-1)	4:1, ±1%

GENERAL SPECIFICATIONS:
OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Safety Standard Undefined.



Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
		Method: Tape & Reel PKG-0410 www.we-online.com/midcom		Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	TRANSFORMER	750314445
6B	9/22	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750314445	SPECIFICATION SHEET 1 OF 1
6A	3/14					

