



**ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:**

D.C. RESISTANCE (@20°C):	2-7 (1+2,6+7), 0.095 Ohms max. 13-9, 0.145 Ohms max.
DIELECTRIC RATING:	500VAC, 1 minute tested by applying 625VAC for 1 second between pins 2-13(1+2).
INDUCTANCE:	272.00μH ±10%, 100kHz, 100mVAC, 0mADC, 2-7, Ls.
TURNS RATIO:	(2-7):(13-9), (8.38):(1.00), ±1%.

Functional Insulation only

OPERATING TEMPERATURE RANGE: -40° to +125°C including temp rise

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

<b>WE-Midcom, Inc.</b> Watertown, SD USA Toll Free: 800-643-2661 Fax: 605-886-4486	Unless otherwise specified, tolerances are as follows: Angles: ±1°      Fractions: ±1/64 Decimals: ±.005 (.127mm)	<b>WE-Midcom, Inc.</b>	
	Drawing Title <h2 style="margin: 0;">Transformer</h2>	Drawing Number <h2 style="margin: 0;">750311310</h2>	Rev. <h2 style="margin: 0;">01</h2>
This drawing is dual dimensioned. Dimensions in brackets are in millimeters	Revisions: See Sheet 1	Scale ----	Sheet 2 of 5
Engineer:TST		04/07/2016	