


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect




ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-3 @20°C	0.131 ohms ±10%
D.C. RESISTANCE	6-4 @20°C	0.172 ohms ±10%
INDUCTANCE	1-3 10kHz, 100mVAC, Ls	22uH ±10%
SATURATION CURRENT	20% rolloff from initial	2.5A
LEAKAGE INDUCTANCE	1-3 tie(6+4), 100kHz, 10mVAC, Ls	120nH typ., 300nH max.
DIELECTRIC	1-6 1500VAC, 1 second	-
TURNS RATIO	(6-4):(1-3)	1.1:1, ±1%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Safety Standard Undefined.



Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0519 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750314712
6B	8/14			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750314712	SPECIFICATION SHEET 1 OF 1
6A	6/14	SEE REVISION SHEET FOR REVISION LEVEL				