

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect





ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	0.51 ohms max.
D.C. RESISTANCE	4-3 @20°C	0.51 ohms max.
INDUCTANCE	1-2 10kHz, 100mVAC, Ls	3.30mH ±30%
INDUCTANCE	4-3 10kHz, 100mVAC, Ls	3.30mH ±30%
DIELECTRIC	1-4 3600VAC, 1 second	3000VAC, 1 minute
TURNS RATIO	(1-2):(4-3)	1:1, ±1%

GENERAL SPECIFICATIONS:
OPERATING TEMPERATURE RANGE: -55°C to +105°C.


CURRENT RATING: 0.8A

Designed to meet 4.0mm min. creepage between winds.



6B Wire insulation & RoHS status not affected by wire color.
6B Wire insulation color may vary depending on availability.

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Fractions: $\pm 1/64$ Decimals: $\pm .005$ [.13] Footprint: $\pm .001$ [.03]	DRAWING TITLE	PART NO.
6C	1/19	Method: Tray PKG-0119 www.we-online.com/midcom		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	INDUCTOR	750311349
6B	3/17	SEE REVISION SHEET FOR REVISION LEVEL			eiSos p/n:	SPECIFICATION SHEET 1 OF 1
6A	12/10				