


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
6B D.C. RESISTANCE	5-8 @20°C	0.150 ohms ±15%
D.C. RESISTANCE	1-4 @20°C	0.197 ohms ±10%
INDUCTANCE	5-8 10kHz, 100mVAC, Ls	26.00uH ±10%
SATURATION CURRENT	5-8 20% rolloff from initial	960mA
6B LEAKAGE INDUCTANCE	5-8 tie(1+4), 100kHz, 100mVAC, Ls	390nH typ., 650nH max.
6B DIELECTRIC	1-8 1875VAC, 2 seconds	1500VAC, 1 minute
URNS RATIO	(1-4):(5-8)	1.09:1, ±1%

GENERAL SPECIFICATIONS:  
OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with the following requirements as defined by IEC61010-1 and IEC61131-2:  
- Minimum creepage distance of 1.6mm for Basic insulation.

Wire insulation & RoHS status not affected by wire color.  
Wire insulation color may vary depending on availability.

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64	DRAWING TITLE	PART NO.
		Method: Tape & Reel PKG-1042 www.we-online.com/midcom		Decimals: ±.005 [ .13] Footprint: ±.005 [ .13]	<b>TRANSFORMER</b>	<b>750315246</b>
6B	7/17	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750315246	SPECIFICATION SHEET 1 OF 1
6A	10/15					

