

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes






ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-6 @20°C	9.00 ohms ±10%
INDUCTANCE	1-6 10kHz, 100mVAC, Ls	5.00mH ±10%
SATURATION CURRENT	20% rolloff from initial	180mA


* DIMENSION MAY BE EXCEEDED WITH SOLDER ONLY

PART MUST INSERT FULLY TO SURFACE A IN RECOMMENDED GRID



Wire insulation & RoHS status not affected by wire color.
 Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications
		Method: Tray PKG-0847 www.we-online.com/midcom
6B	5/20	
6A	11/10	SEE REVISION SHEET FOR



Tolerances unless otherwise specified:
 Angles: ±1°
 Fractions: ±1/64
 Decimals: ±.005 [0.13]
 Footprint: ±.001 [0.03]
 This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

DRAWING TITLE
TRANSFORMER
 eiSos p/n: 750311909

PART NO.
750311909
 SPECIFICATION SHEET 1 OF 1

