



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-3 @20°C	0.125 ohms max.
D.C. RESISTANCE	6-4 @20°C	15.00 ohms max.
INDUCTANCE	1-3 100kHz, 100mVAC, Ls	5.0uH ±10%
LEAKAGE INDUCTANCE	1-3 tie(4+6), 100kHz, 10mVAC, Ls	300nH max.
DIELECTRIC	1-6 600VAC, 1 second	-
TURNS RATIO	(6-4):(1-3)	19.1:1, ±2%
TURNS RATIO	(6-5):(5-4)	1:1, ±2%



GENERAL SPECIFICATIONS:
OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.
 Safety Standard Undefined.

Wire insulation & RoHS status not affected by wire color.
 Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0637 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750312154
6A	11/11	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750312154	SPECIFICATION SHEET 1 OF 1