


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
6B D.C. RESISTANCE	5-8 @20°C	0.167 ohms ±15%
6B D.C. RESISTANCE	1-4 @20°C	0.395 ohms ±10%
INDUCTANCE	5-8 10kHz, 100mVAC, Ls	30uH ±10%
SATURATION CURRENT	5-8 20% rolloff from initial	880mA
6B LEAKAGE INDUCTANCE	5-8 tie(1+4), 100kHz, 100mVAC, Ls	550nH typ., 825nH max.
6B DIELECTRIC	1-8 1875VAC, 2 seconds	1500VAC, 1 minute
URNS RATIO	(1-4):(5-8)	2:1, ±1%

GENERAL SPECIFICATIONS:
 OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with the following requirements as defined by IEC61010-1 and IEC61131-2:
 - Minimum creepage distance of 1.6mm for Basic insulation.

Wire insulation & RoHS status not affected by wire color.
 Wire insulation color may vary depending on availability.

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Fractions: $\pm 1/64$	DRAWING TITLE	PART NO.
		Method: Tape & Reel PKG-1042 www.we-online.com/midcom		Decimals: $\pm .005$ [.13] Footprint: $\pm .005$ [.13]	TRANSFORMER	750315247
6B	7/17	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750315247	SPECIFICATION SHEET 1 OF 1
6A	10/15					