

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn100%	Yes	Yes

more than you expect




ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	5-2 @20°C	2.15 ohms ±10%
INDUCTANCE	5-2 10kHz, 100mVAC, Ls	3.5mH ±10%
SATURATION CURRENT	20% rolloff from initial	2A

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.



Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-0028 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.001 [.03]	DRAWING TITLE INDUCTOR	PART NO. 750312352
6B	12/12			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750312352	compliant RoHS
6A	8/11	SEE REVISION SHEET FOR REVISION LEVEL				