





CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn98%, Cu2%	Yes	Yes

TERM. NO.'s FOR REF. ONLY



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-8 @20°C	.720 ohms max.
D.C. RESISTANCE	2-7 @20°C	.770 ohms max.
D.C. RESISTANCE	4-5 @20°C	.560 ohms max.
INDUCTANCE	1-8 100kHz, 10mVAC, Ls	39uH±20%
LEAKAGE INDUCTANCE	1-8 tie(2+4+5+7), 100kHz, 100mVAC, Ls	3uH max.
DIELECTRIC	1-4 1875Vdc, 1 second	1500Vdc, 1 minute
URNS RATIO	(2-7):(1-8)	1.18:1, ±2%
URNS RATIO	(4-5):(1-8)	1.18:1, ±2%



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +85°C.

Undefined Standard:

- Basic Insulation
- 1.4mm Creepage & Clearance.

PRELIMINARY

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0576 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750315379
01	3/15	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750315379	SPECIFICATION SHEET 1 OF 1