


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



**ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:**

D.C. RESISTANCE (@20°C):	2-6 (tie 2+3, 5+6), 0.008 Ohms max. 13-11, 0.420 Ohms ±10%. 9-8, 0.039 Ohms ±20%.
DIELECTRIC RATING:	1250VAC for 1 second between pins 2-13 (tie 5+6, 9+11).
INDUCTANCE:	12.0 µH ±10%, 10kHz, 100mVAC, 0mADC, 2-6(tie 2+3, 5+6), Ls.
LEAKAGE INDUCTANCE:	2.2µH ±10%, 100kHz, 100mVAC, 2-6(tie 2+3, 5+6, 9+8, 13+11), Ls.
TURNS RATIO:	( 13-11 ):( 2-6 ), ( 12 ):(1.00), (tie 2+3, 5+6), ±1%. ( 13-11 ):( 9-8 ), ( 36 ):(1.00), ±1%.

OPERATING TEMPERATURE RANGE: -40°C to 125°C including temp. rise.

Safety Standard Undefined

T\_8\_2New

<b>WE-Midcom, Inc.</b> Watertown, SD USA Toll Free: 800-643-2661 Fax: 605-886-4486	Unless otherwise specified, tolerances are as follows: Angles: ±1°      Fractions: ±1/64 Decimals: ±.005 (.127mm)		<b>WE-Midcom, Inc.</b>	
	Drawing Title <h1>Transformer</h1>		Drawing Number <h2>750313131</h2>	Rev. 00
Revisions: See Sheet 1		Scale ----	Spec Sheet 1 of 1	
This drawing is dual dimensioned. Dimensions in brackets are in millimeters			Engineer: JJB      03/29/2012	