




CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-10 @20°C	1.55 ohms ±10%
INDUCTANCE	1-10 10kHz, 100mV, Ls	1.20mH ±10%
SATURATION CURRENT	1-10 20% rolloff from initial	850mA
DIELECTRIC	1-core 625VDC, 1 second	500VDC, 1 minute




GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Safety standard undefined

Reference Design

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM	SP	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
DATE	3/18/2015	Method: Tray		Angles: $\pm 1^\circ$ Decimals: $\pm .005$ [.13]		
ENG	EJK	PKG-0816		Fractions: $\pm 1/64$ Footprint: $\pm .001$ [.03]		
REV.	02			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		
DATE	1/5/2016	www.we-online.com/midcom				
				INDUCTOR	750315453	
						SPECIFICATION SHEET 1 OF 1