




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



**ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:**

D.C. RESISTANCE (@20°C):	1-14 , 0.130 Ohms ±10%. 2-13 , 0.085 Ohms ±20%. 4-11 , 0.025 Ohms max. 5-10 , 0.025 Ohms max. 6-9 , 0.025 Ohms max. 7-8 , 0.025 Ohms max.
DIELECTRIC RATING:	3000VAC, 1 minute tested by applying 3750VAC for 1 second between pins 1-4(tie 8+9+10+11, 13+14). 500VAC, 1 minute tested by applying 625VAC for 1 second between pins 1-2.
INDUCTANCE:	250µH ±10%, 10kHz, 100mVAC, 0mADC, 1-14, Ls.
SATURATION CURRENT:	5A saturating current that causes 20% rolloff from initial inductance.
LEAKAGE INDUCTANCE:	5.5µH typ, 10µH max, 100kHz, 100mVAC, 1-14(tie 2+13, 4+5+6+7+9+8+10+11), Ls.
TURNS RATIO:	( 1-14 ):( 2-13 ) , ( 5 ):(1.00) , ±1%. ( 1-14 ):( 4-11 ) , ( 8.75 ):(1.00) , ±1%. ( 1-14 ):( 5-10 ) , ( 8.75 ):(1.00) , ±1%. ( 1-14 ):( 6-9 ) , ( 8.75 ):(1.00) , ±1%. ( 1-14 ):( 7-8 ) , ( 8.75 ):(1.00) , ±1%.

Safety Standard Undefined

OPERATING TEMPERATURE RANGE: -40°C to 125°C including temp. rise.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

WE-Midcom, Inc. Watertown, SD USA Toll Free: 800-643-2661 Fax: 605-886-4486	Unless otherwise specified, tolerances are as follows: Angles: ±1°      Fractions: ±1/64 Decimals: ±.005 (.127mm)		WE-Midcom, Inc.	
	Drawing Title <b>Transformer</b>		Drawing Number <b>750313219</b>	Rev. <b>01</b>
Revisions: See Sheet 1		Scale ----	Spec Sheet 1 of 1	
Engineer:LJG			06/22/2012	

This drawing is dual dimensioned. Dimensions in brackets are in millimeters