



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

- D.C. RESISTANCE (@20°C): 1-4 (1+2+3, 4+5+6), 0.007 Ohms max.
7-10 (7+8+9, 10+11+12), 0.009 Ohms max.
- DIELECTRIC RATING: 1000VAC, 1 minute tested by applying 1250VAC for 1 second between pins 1-12.
- INDUCTANCE: 1.50µH ±10%, 100kHz, 100mVAC, 0mADC, 1-4(1+2+3,4+5+6), Ls.
- SATURATION CURRENT: >20A saturating current that causes 20% rolloff from initial inductance.
- LEAKAGE INDUCTANCE: 150nH typ., 350nH max., 100kHz, 100mVAC, 1-4(1+2+3, 4+5+6, 7+8+9+10+11+12), Ls.
- URNS RATIO: (1-4):(12-9), (1):(1.00), tie(1+2+3,4+5+6, 7+8+9, 10+11+12), ±1%.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

WE-Midcom, Inc. Watertown, SD USA Toll Free: 800-643-2661 Fax: 605-886-4486	Unless otherwise specified, tolerances are as follows: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 (.127mm)		WE-Midcom, Inc.	
	Drawing Title <h1>Transformer</h1>		Drawing Number <h2>750313394</h2>	Rev. 00
This drawing is dual dimensioned. Dimensions in brackets are in millimeters	Revisions: See Sheet 1		Scale ----	Spec Sheet 1 of 1
Engineer:PLP			07/20/2012	