

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes







ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-3 @20°C	1.75 ohms ±10%
D.C. RESISTANCE	7-9 @20°C	0.070 ohms max.
INDUCTANCE	1-3 10kHz, 100mVAC, Ls	1.59mH ±10%
SATURATION CURRENT	1-3 20% rolloff from initial	600mA
LEAKAGE INDUCTANCE	1-3 tie(7+9), 100kHz, 100mVAC, Ls	20uH typ., 40uH max.
DIELECTRIC	3-9 1875VAC, 1 second	1500VAC, 1 minute
URNS RATIO	(3-1):(9-7)	6.25:1, ±1%

GENERAL SPECIFICATIONS:
Safety Standard Undefined.

TERM. NO.'s FOR REF. ONLY



Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
		Method: Tape & Reel PKG-0499 www.we-online.com/midcom		Angles: $\pm 1^\circ$ Fractions: $\pm 1/64$	TRANSFORMER	750313829
6B	9/22			Decimals: $\pm .005$ [.13] Footprint: $\pm .005$ [.13]		
6A	10/15	SEE REVISION SHEET FOR	REVISION LEVEL	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750313829	SPECIFICATION SHEET 1 OF 1

