



CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect




ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	4-3 @20°C	1.14 ohms ±10%
D.C. RESISTANCE	6-8 @20°C	0.045 ohms ±20%
INDUCTANCE	4-3 10kHz, 100mV, Ls	880µH ±10%
SATURATION CURRENT	4-3 20% rolloff from initial	600mA
LEAKAGE INDUCTANCE	4-3 tie(6+8), 100kHz, 100mV, Ls	3.7µH typ., 7.4µH max.
DIELECTRIC	2-8 625VAC, 1 second	
TURNS RATIO	(2-3):(4-2)	1:1, ±1%
TURNS RATIO	(4-3):(6-8)	4.47:1, ±1%



RECOMMENDED P.C. PATTERN, COMPONENT SIDE



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

- Functional insulation only

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM	SP	Packaging Specifications		Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.001 [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750315761
DATE	8/27/2015	Method: Tray				
ENG	KLM	PKG-0168				
REV.	00					
DATE	10/1/2015	www.we-online.com/midcom				