




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

D.C. RESISTANCE (@20°C):	1-3 , 0.017 Ohms \pm 20%. 6-10 , 0.027 Ohms \pm 20%. 7-9 , 0.013 Ohms max.
DIELECTRIC RATING:	1500VAC for 1 second between pins 1-10(tie 6+7).
INDUCTANCE:	80 μ H \pm 20%, 10kHz, 100mVAC, 0mADC, 1-3, Ls.
LEAKAGE INDUCTANCE:	270nH typ, 500nH max, 100kHz, 100mVAC, 1-3(tie 6+7+9+10), Ls.
URNS RATIO:	(1-3):(7-9) , (2.67):(1.00) , \pm 1%. (10-6):(1-3) , (1.13):(1.00) , \pm 1%.

OPERATING TEMPERATURE RANGE: -40°C to 125°C including temp. rise.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

Wurth Electronics Midcom Inc. Watertown, SD USA Toll Free: 800-643-2661 Fax: 605-886-4486	Unless otherwise specified, tolerances are as follows: Angles: \pm 1° Fractions: \pm 1/64 Decimals: \pm .005(.127mm) Footprint: \pm .005(.13mm)		more than you expect	
	Drawing Title Transformer		Drawing Number 750314853	Rev. 00
This drawing is dual dimensioned. Dimensions in brackets are in millimeters		Revisions: See Sheet 1		Scale ---- Spec Sheet 1 of 1

Engineer:LJG

06/03/2014