




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-11 @20°C	0.223 ohms ±10%
INDUCTANCE	2-11 100kHz, 100mVAC, Ls	240uH ±10%
INDUCTANCE	2-11 100kHz, 100mVAC, 6ADC, Ls	240uH ±10%
SATURATION CURRENT	2-11 20% rolloff from initial	9.8A
DIELECTRIC	2-Core 625VAC, 1 second	500VAC, 1 minute

GENERAL SPECIFICATIONS:
 OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.
 Safety standard undefined.



Wire insulation & RoHS status not affected by wire color.
 Wire insulation color may vary depending on availability.

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64	DRAWING TITLE	PART NO.
		Method: Tray PKG-1175 www.we-online.com/midcom		Decimals: ±.005 [.13] Footprint: ±.001 [.03]	INDUCTOR	750317130
6B	5/23	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750317130	SPECIFICATION SHEET 1 OF 1
6A	10/17					

