


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:



PARAMETER	TEST CONDITIONS	VALUE
6B D.C. RESISTANCE	1-4 @20°C	0.190 ohms ±10%
6B D.C. RESISTANCE	5-8 @20°C	0.161 ohms ±15%
INDUCTANCE	5-8 10kHz, 100mVAC, Ls	30uH ±10%
SATURATION CURRENT	5-8 20% rolloff from initial	960mA
6B LEAKAGE INDUCTANCE	5-8 tie(1+4), 100kHz, 100mVAC, Ls	500nH typ., 750nH max.
6B DIELECTRIC	1-8 1875VAC, 2 seconds	1500VAC, 1 minute
URNS RATIO	(5-8):(1-4)	1:1, ±1%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with the following requirements as defined by IEC61010-1 and IEC61131-2:

- Minimum creepage distance of 1.6mm for Basic insulation.



Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications		Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
		Method: Tape & Reel		Angles: ±1°	TRANSFORMER	750315245
		PKG-1042		Decimals: ±.005 [1.3]		
		www.we-online.com/midcom		Fractions: ±1/64		
6B	7/17	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750315245	SPECIFICATION SHEET 1 OF 1
6A	10/15					