




CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-4 @20°C	0.900 ohms ±10%
INDUCTANCE	1-4 10kHz, 100mV, Ls	660µH ±10%
SATURATION CURRENT	1-4 20% rolloff from initial	2A



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.
 Safety standard undefined

Reference Design

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM	SP	Packaging Specifications	<p>CONVENTION PLACEMENT</p>	Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Decimals: $\pm .005$ [.13] Fractions: $\pm 1/64$ Footprint: $\pm .001$ [.03]	DRAWING TITLE INDUCTOR	PART NO. 750315291
DATE	12/22/2014	Method: Tray		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		
ENG	TST	PKG-0199				
REV.	00					
DATE	2/24/2015	www.we-online.com/midcom				SPECIFICATION SHEET 1 OF 1