


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes




ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	15.40 mOhms max.
D.C. RESISTANCE	4-3 @20°C	15.40 mOhms max.
INDUCTANCE	1-2 10kHz, 100mVAC, Ls	802uH ±38%
INDUCTANCE	4-3 10kHz, 100mVAC, Ls	802uH ±38%
DIELECTRIC	1-4 1200VAC, 2 seconds	-
URNS RATIO	(1-2):(4-3)	1:1, ±2%



PART MUST INSERT FULLY TO SURFACE A IN RECOMMENDED GRID  
 $\varnothing.039(4)$   
 [1.00]



TERM. NO.'s FOR REFERENCE ONLY



LOT CODE & DATE CODE



RECOMMENDED  
 P.C. PATTERN, COMPONENT SIDE

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

CURRENT RATING: 5ADC

Wire insulation & RoHS status not affected by wire color.  
 Wire insulation color may vary depending on availability.

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications Method: Tray PKG-0712 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Fractions: $\pm 1/64$ Decimals: $\pm .005$ [.13] Footprint: $\pm .001$ [.03]	DRAWING TITLE <b>INDUCTOR</b> COMMON MODE CHOKE eiSos p/n: 750318019	PART NO. <b>750318019</b>
6A	8/19	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		SPECIFICATION SHEET 1 OF 1