

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect





ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-6 tie(1+2+3, 4+5+6), @20°C	0.170 ohms ±10%
INDUCTANCE	1-6 tie(1+2+3, 4+5+6), 10kHz, 100mVAC, Ls	350uH ±10%
SATURATION CURRENT	1-6 tie(1+2+3, 4+5+6), 20% rolloff from initial	15A

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Functional insulation only.



Customer to tie terminals 1&2&3 and 4&5&6 on PC board.

Application of the transformer allows for the leadwires between terminals 1&2&3 and 4&5&6 to solder bridge.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-0825 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Fractions: $\pm 1/64$ Decimals: $\pm .005$ [.13] Footprint: $\pm .001$ [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750315797
6A	9/16	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750315797	SPECIFICATION SHEET 1 OF 1