


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes




PART MUST INSERT FULLY TO SURFACE A IN RECOMMENDED GRID

∅.031(11)  
[.80]



TERM. NO.'s FOR REF. ONLY

DOT LOCATES TERM. #1



LOT CODE & DATE CODE


**ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:**

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-5 tie(2+3, 4+5), @20°C	0.096 ohms ±10%
INDUCTANCE	2-5 tie(2+3, 4+5), 10kHz, 100mVAC, Ls	350uH ±15%
SATURATION CURRENT	2-5 tie(2+3, 4+5), 20% rolloff from initial	15A

**GENERAL SPECIFICATIONS:**


OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Functional insulation only.



Customer to tie terminals 2+3 and 4+5 on PC board.

Application of the transformer allows for the leadwires between terminals 2&3 and 4&5 to solder bridge.



RECOMMENDED P.C. PATTERN, COMPONENT SIDE

Wire insulation & RoHS status not affected by wire color.  
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: <b>Tape &amp; Reel</b> PKG-1241 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [ .13 ] Footprint: ±.001 [ .03 ]	DRAWING TITLE <b>INDUCTOR</b>	PART NO. <b>750318020</b>
6A	12/20	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750318020	SPECIFICATION SHEET 1 OF 1