


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



* START LEAD EXITS COIL ON TERMINAL SIDE



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2	@20°C
D.C. RESISTANCE	3-4	@20°C
D.C. RESISTANCE	S-F	@20°C
D.C. RESISTANCE	3-5	@20°C
D.C. RESISTANCE	2-6	@20°C
INDUCTANCE	1-6	10kHz, 100mVAC, Ls
SATURATION CURRENT	1-6	20% rolloff from initial
LEAKAGE INDUCTANCE	1-6	tie(S+F, 3+4+5), 100kHz, 100mVAC, Ls
DIELECTRIC	6-S	tie(5+6), 3750VAC, 1 second
URNS RATIO	(1-6):(S-F)	13:1, ±1%
URNS RATIO	(1-6):(3-4)	4:1, ±1%
URNS RATIO	(1-6):(5-3)	5.78:1, ±1%
URNS RATIO	(1-2):(2-6)	1:1, ±1%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with the following requirements as defined by IEC60950-1, EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:

- Reinforced insulation for a primary circuit at a working voltage of 265Vrms, 400Vpeak, Overvoltage Category II.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
		Method: Tray PKG-0936 www.we-online.com/midcom		Angles: ±1° Fractions: ±1/64 Decimals: ±.005 Footprint: ±.001	TRANSFORMER	750315841
6A	12/16	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750315841	SPECIFICATION SHEET 1 OF 1

