


| CUSTOMER TERMINAL | RoHS | LEAD(Pb)-FREE |
|-------------------|------|---------------|
| Sn96%, Ag4% | Yes | Yes |

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

| PARAMETER | TEST CONDITIONS | VALUE |
|--------------------|-----------------------------------|--------------------------|
| D.C. RESISTANCE | 2-4 @20°C | 0.980 ohms ±10% |
| D.C. RESISTANCE | 9-7 @20°C | 0.325 ohms ±10% |
| INDUCTANCE | 2-4 10kHz, 100mVAC, Ls | 830uH ±10% |
| SATURATION CURRENT | 2-4 20% rolloff from initial | 1.6A |
| LEAKAGE INDUCTANCE | 2-4 tie(7+9), 100kHz, 100mVAC, Ls | 22.0uH typ., 44.0uH max. |
| DIELECTRIC | 2-9 1500VAC, 1 second | - |
| ⑥B TURNS RATIO | (2-4):(9-7) | 2.27:1 |

GENERAL SPECIFICATIONS:
OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.
Functional insulation only.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

| REV. | DATE | Packaging Specifications | | Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 | Decimals: ±.005 Footprint: ±.001 | DRAWING TITLE | PART NO. |
|------|------|--|----------------------|--|-------------------------------------|----------------------|----------------------------|
| | | Method: Tray PKG-0736 www.we-online.com/midcom | CONVENTION PLACEMENT | | | TRANSFORMER | 750316266 |
| 6B | 4/23 | SEE REVISION SHEET FOR REVISION LEVEL | | This drawing is dual dimensioned. Dimensions in brackets are in millimeters. | | eiSos p/n: 750316266 | SPECIFICATION SHEET 1 OF 1 |
| 6A | 2/17 | | | | | | |