



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	3-10 tie(4+9), @20°C	5.55 ohms \pm 10%
INDUCTANCE	3-10 tie(4+9), 10kHz, 100mVAC, Ls	100mH \pm 10%
SATURATION CURRENT	3-10 tie(4+9), 20% rolloff from initial	200mA
DIELECTRIC	3-9 625VAC, 1 second	500VAC, 1 minute
URNS RATIO	(3-4):(9-10)	1:1, \pm 1%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-0825 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: \pm 1° Fractions: \pm 1/64 Decimals: \pm .005 [.13] Footprint: \pm .001 [.03]	DRAWING TITLE INDUCTOR	PART NO. 750318652
6A	4/20	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750318652	SPECIFICATION SHEET 1 OF 1