



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect




TERM. NO.'s FOR REF. ONLY




DOT LOCATES TERM. #1

LOT CODE & DATE CODE



Customer to tie 2+3 on board



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	0.32 ohms max.
D.C. RESISTANCE	3-4 @20°C	0.32 ohms max.
D.C. RESISTANCE	5-8 @20°C	0.41 ohms max.
INDUCTANCE	1-2 100kHz, 100mVAC, Ls	22uH ±10%
LEAKAGE INDUCTANCE	1-2 tie(3+4, 5+8), 100kHz, 100mVAC, Ls	2uH max.
DIELECTRIC	1-8 tie(2+3), 1875VAC, 1 second	1500VAC, 1 minute
TURNS RATIO	(3-4):(1-2)	1:1, ±1%
TURNS RATIO	(5-8):(1-2)	1:1, ±1%

REV.	DATE	Packaging Specifications
		Method: Tape & Reel
		PKG-0328
		www.we-online.com/midcom
6A	7/10	SEE REVISION SHEET FOR REVISION LEVEL



Tolerances unless otherwise specified:
 Angles: ±1° Decimals: ±.005 [.13]
 Fractions: ±1/64 Footprint: ±.005 [.13]

This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

DRAWING TITLE
TRANSFORMER

eiSos p/n: **750340727**

PART NO.
750340727

SPECIFICATION SHEET 1 OF 1

