




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	0.310 ohms max.
D.C. RESISTANCE	5-6 @20°C	0.165 ohms max.
D.C. RESISTANCE	FS-FF @20°C	0.028 ohms max.
INDUCTANCE	1-2 65kHz, 1.00VAC, Ls	0.400mH $\pm$ 10%
LEAKAGE INDUCTANCE	1-2 tie(FS+FF), 65kHz, 1.00VAC, Ls	5.00uH max.
DIELECTRIC	1-FS tie(3+5+core), 3600VAC, 1 second	-
URNS RATIO	(1-2):(5-6)	6:1, $\pm$ 2%
URNS RATIO	(1-2):(FS-FF)	3.6:1, $\pm$ 2%



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C.

Wire insulation & RoHS status not affected by wire color.  
Wire insulation color may vary depending on availability.

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications Method: Tray PKG-0253 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: $\pm$ 1°      Decimals: $\pm$ .005 [.13] Fractions: $\pm$ 1/64      Footprint: $\pm$ .001 [.03]	DRAWING TITLE <b>TRANSFORMER</b>	PART NO. <b>750340828</b>
6A	2/11	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750340828	SPECIFICATION SHEET 1 OF 1