



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	0.3 ohms max.
D.C. RESISTANCE	3-4 @20°C	0.17 ohms max.
INDUCTANCE	1-2 10kHz, 100mVAC, Ls	62uH min.
DIELECTRIC	1-4 3750VAC, 1 second	3000VAC, 1 minute
TURNS RATIO	(4-3):(1-2)	1:1, ±1%



GENERAL SPECIFICATIONS:

Designed to comply with the following requirements as defined by IEC60950-1, EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:
 - Supplementary insulation for a primary circuit at a working voltage of 250Vrms.
 Designed to meet 5kV (1.2x50usec) surge test.

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT
		Method: Tape & Reel PKG-0376 www.we-online.com/midcom	
6B	2/22		
6A	1/13	SEE REVISION SHEET FOR REVISION LEVEL	

Tolerances unless otherwise specified:
 Angles: ±1°
 Fractions: ±1/64
 Decimals: ±.005 [.13]
 Footprint: ±.005 [.13]
 This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

DRAWING TITLE
TRANSFORMER
 eiSos p/n: 750340848

PART NO.
750340848
 SPECIFICATION SHEET 1 OF 1

