



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



TERM. NO.'s FOR REF. ONLY





DOT LOCATES TERM. #1

LOT CODE & DATE CODE

PRI
5V
200kHz

SEC
3.8V, 1.2A



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-1 @20°C	0.055 ohms max.
D.C. RESISTANCE	2-3 @20°C	0.055 ohms max.
D.C. RESISTANCE	6-7 @20°C	0.070 ohms max.
D.C. RESISTANCE	7-8 @20°C	0.070 ohms max.
INDUCTANCE	1-2 10kHz, 100mVAC, Ls	48.0uH min.
DIELECTRIC	2-7 1250VAC, 1 second	-
URNS RATIO	(1-2):(2-3)	1:1, ±2%
URNS RATIO	(1-2):(8-7)	1:1, ±2%
URNS RATIO	(1-2):(7-6)	1:1, ±2%

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0328 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750341004
6B	10/13	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750341004	SPECIFICATION SHEET 1 OF 1
6A	6/13		REVISION LEVEL			

