



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect




ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-4 @20°C	2.70 ohms max.
D.C. RESISTANCE	5-6 @20°C	0.43 ohms max.
D.C. RESISTANCE	7-6 @20°C	0.43 ohms max.
INDUCTANCE	1-4 10kHz,100mVAC, Ls	4.5mH ±10%
LEAKAGE INDUCTANCE	1-4 tie(5+6+7+8), 10kHz, 100mVAC, Ls	840uH-920uH
DIELECTRIC	tie(6+7), 1000VAC, 1 second	
URNS RATIO	(1-4):(5-6)	5.5:1, ±2%
URNS RATIO	(1-4):(7-8)	5.5:1, ±2%

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications
		Method: Tray PKG-0199 www.we-online.com/midcom
00	6/11	SEE REVISION SHEET FOR REVISION LEVEL



Tolerances unless otherwise specified:
Angles: ±1°
Fractions: ±1/64
Decimals: ±.005 [.13]
Footprint: ±.001 [.03]

This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

DRAWING TITLE
LLC TRANSFORMER

eiSos p/n: 750341120



PART NO.
750341120
SPECIFICATION SHEET 1 OF 1