


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



PART MUST INSERT FULLY TO SURFACE A IN RECOMMENDED GRID
 $\phi.031(5)$
 [.80]





ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	4-5 @20°C	0.188 ohms ±10%
D.C. RESISTANCE	8-11 @20°C	0.084 ohms ±20%
INDUCTANCE	8-11 10kHz, 100mVAC, Ls	250.00uH ±10%
SATURATION CURRENT	8-11 20% rolloff from initial	9.1A
DIELECTRIC	4-11 625VAC, 1 second	-
URNS RATIO	(11-8):(5-4)	8.75:1, ±1%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.



Wire insulation & RoHS status not affected by wire color.
 Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-1041 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.001 [.03]	DRAWING TITLE INDUCTOR	PART NO. 750317636
6B	2/19			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750317636	SPECIFICATION SHEET 1 OF 1
6A	12/18	SEE REVISION SHEET FOR REVISION LEVEL				