


CUSTOMER	TERMINAL	RoHS	LEAD(Pb)-FREE
Sn100%	Yes	Yes	



more than you expect



* DIMENSION MAY BE EXCEEDED WITH SOLDER ONLY



PART MUST INSERT FULLY TO SURFACE A IN RECOMMENDED GRID



RECOMMENDED
P.C. PATTERN, COMPONENT SIDE

ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	3-2 @20°C	0.745 ohms max.
D.C. RESISTANCE	2-1 @20°C	1.046 ohms max.
D.C. RESISTANCE	5-6 @20°C	0.634 ohms max.
D.C. RESISTANCE	6-7 @20°C	0.392 ohms max.
D.C. RESISTANCE	13-14 @20°C	0.054 ohms max.
D.C. RESISTANCE	10-11 @20°C	0.131 ohms max.
D.C. RESISTANCE	9-8 @20°C	0.053 ohms max.
INDUCTANCE	3-1 10kHz, 100mVAC, Ls	3.4mH ±10%
DIELECTRIC	tie(3+5,9+10,11+13), 3750VAC, 1 second	-
DIELECTRIC	3-5 1500VAC, 1 second	-
URNS RATIO	(3-1):(5-6)	17.6:1, ±2%
URNS RATIO	(3-1):(6-7)	29.3:1, ±2%
URNS RATIO	(3-1):(13-14)	13.5:1, ±2%
URNS RATIO	(3-1):(10-11)	11.7:1, ±2%
URNS RATIO	(3-1):(9-8)	35.2:1, ±2%

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG- www.we-online.com/midcom	CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.001 [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750341470
00	05/12	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750341470	SPECIFICATION SHEET 1 OF 1

