

CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes



more than you expect




ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2A-3A @20°C	0.018 ohms max.
D.C. RESISTANCE	8A-9A @20°C	0.020 ohms max.
INDUCTANCE	2A-3A 10kHz, 100mV, Ls	62.40μH ±10%
SATURATION CURRENT	2A-3A 20% rolloff from initial	40A
LEAKAGE INDUCTANCE	2A-3A tie(8A+9A), 100kHz, 100mV, Ls	4.5μH typ.
DISTRIBUTED CAPACITANCE	2A-3A 100mVAC, Cs	80.0pF typ.
INTERWINDING CAPACITANCE	2A-8A 100kHz, 10mVAC, Cs	135.0pF typ.
DIELECTRIC	2A-8A 4000VDC, 1 second	4000VDC, 1 minute
URNS RATIO	(2A-3A):(8A-9A)	1.11:1, ±1%


PART MUST INSERT FULLY TO SURFACE A IN RECOMMENDED GRID



TERM. NO.'s FOR REF. ONLY



RECOMMENDED P.C. PATTERN, COMPONENT SIDE



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.
Safety standard undefined

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM	SP	Packaging Specifications	
DATE	8/8/2018	Method: Tray	
ENG	CHC	PKG-0086	<p>CONVENTION PLACEMENT</p> <p>This drawing is dual dimensioned. Dimensions in brackets are in millimeters.</p>
REV.	01		
DATE	1/2/2019	www.we-online.com/midcom	

Tolerances unless otherwise specified:	
Angles: $\pm 1^\circ$	Decimals: $\pm .005$ [.13]
Fractions: $\pm 1/64$	Footprint: $\pm .001$ [.03]

DRAWING TITLE
TRANSFORMER

PART NO.
750317867
SPECIFICATION SHEET 1 OF 1