



| | | |
|-------------------|------|---------------|
| CUSTOMER TERMINAL | RoHS | LEAD(Pb)-FREE |
| Sn96%, Ag4% | Yes | Yes |



Midcom



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

| PARAMETER | TEST CONDITIONS | VALUE |
|-----------------|-----------------------|-------------|
| D.C. RESISTANCE | 7-1 @20°C | 1.329 max. |
| D.C. RESISTANCE | 5-4 @20°C | 0.650 max. |
| INDUCTANCE | 7-1 20kHz, 1.0VAC, Ls | 700.0uH ±5% |
| DIELECTRIC | 1-4 1800VAC, 1 second | - |
| URNS RATIO | (7-1):(5-4) | 5.0:1, ±2% |

GENERAL SPECIFICATIONS:
OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

| | | | | | | |
|------|------|--|--|--|----------------------------------|----------------------------|
| REV. | DATE | Packaging Specifications Method: Tray PKG-0816 www.we-online.com/midcom | | Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 Footprint: ±.001 | DRAWING TITLE INDUCTOR | PART NO. |
| 6B | 5/13 | SEE REVISION SHEET FOR REVISION LEVEL | | This drawing is dual dimensioned. Dimensions in brackets are in millimeters. | eiSos p/n: 750341595 | 750341595 |
| 6A | 1/13 | | | | | SPECIFICATION SHEET 1 OF 1 |