



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes




ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-7 tie(1+2+3, 5+6+7), @20°C	0.012 ohms ±25%
D.C. RESISTANCE	9-13 @20°C	0.051 ohms ±20%
INDUCTANCE	1-7 tie(1+2+3, 5+6+7), 10kHz, 100mVAC, Ls	25.0uH ±10%
SATURATION CURRENT	1-7 tie(1+2+3, 5+6+7), 20% rolloff from initial	24.5A
LEAKAGE INDUCTANCE	1-7 tie(1+2+3, 5+6+7, 9+13), 100kHz, 100mVAC, Ls	2.5uH typ., 5.0uH max.
DIELECTRIC	1-13 tie(5+6+7), 500VAC, 1 second	-
URNS RATIO	(1-7):(13-9), tie(1+2+3, 5+6+7)	1:1



Application of the transformer allows for the leadwires between terminals 1&2&3 and 5&6&7 to solder bridge.



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Functional insulation only.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-0904 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.001 [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750318760
6A	6/23	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750318760	SPECIFICATION SHEET 1 OF 1