


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-1 @20°C	8.70 ohms max.
D.C. RESISTANCE	4-3 @20°C	1.57 ohms max.
D.C. RESISTANCE	8-5 @20°C	0.41 ohms max.
INDUCTANCE	2-1 50kHz, 1.0VAC, Ls	7.7 mH ±10%
INDUCTANCE LEAKAGE	2-1 tie(3+4,5+8), 50KHz, 1.0VAC, Ls	230 uH max.
DIELECTRIC	1-8 tie(2+3), 625VAC, 1 second	500VAC, 1 minute
TURNS RATIO	(2-1):(8-5)	7.586:1, ±2%
TURNS RATIO	(2-1):(4-3)	6.111:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0328 www.midcom-inc.com		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750341854
01	5/13	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750341854	SPECIFICATION SHEET 1 OF 1
00	4/13					