




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-4 @20°C	6.89 ohms max.
D.C. RESISTANCE	5-7 @20°C	6.66 ohms max.
INDUCTANCE	1-4 50kHz, 100mVAC, Ls	1.39 mH ±10%
DIELECTRIC	1-7 625VAC, 1 second	500VAC, 1 minute
URNS RATIO	(1-4):(7-5)	2.698:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

REFERENCE DESIGN

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: TAPE&REEL PKG-0328 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.001 [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750342001
01	10/13	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750342001	
00	7/13					compliant RoHS SPECIFICATION SHEET 1 OF 1