


CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect




PART MUST INSERT FULLY TO SURFACE A IN RECOMMENDED GRID
 $\phi .031(10)$
 [.80]

* DIMENSION MAY BE EXCEEDED WITH SOLDER ONLY



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:


PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-5 tie(2+3, 4+5), @20°C	0.285 ohms ±10%
INDUCTANCE	2-5 tie(2+3, 4+5), 10kHz, 100mV, Ls	680µH ±10%
SATURATION CURRENT	2-5 tie(2+3, 4+5), 20% rolloff from initial	4.75A



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

- Functional insulation only



Application of the transformer allows for the leadwires between terminals 2&3 and 4&5 to solder bridge.

Customer to tie terminals 2+3 and 4+5 on PC board.

Preliminary

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability. Marking detail font and color may vary on preproduction samples.

DFM	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.001 [.03]	DRAWING TITLE	PART NO.
DATE	Method: Tray		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	INDUCTOR	750319295
ENG	PKG-0807				
REV.	00				
DATE	7/21/2020	www.we-online.com/midcom			SPECIFICATION SHEET 1 OF 1