


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER		TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-3	@20°C	0.100 ohms max.
D.C. RESISTANCE	6-4	@20°C	0.100 ohms max.
INDUCTANCE	1-3	10kHz, 100mVAC, Ls	68.00uH min.
LEAKAGE INDUCTANCE	1-3	tie(6+4), 100kHz, 100mVAC, Ls	1.45uH typ., 2.20uH max.
INTERWINDING CAPACITANCE	1-6	100kHz, 10mVAC, Cs	3.9pF typ.
DIELECTRIC	1-6	3125VAC, 1 second	-
URNS RATIO		(1-3):(6-4)	1:1

GENERAL SPECIFICATIONS:
 OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.
 VOLTAGE-TIME: 7.7Vus for Unipolar operation
 15.4Vus for Bipolar operation



Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
		Method: Tape & Reel PKG-1054 www.we-online.com/midcom		Angles: $\pm 1^\circ$ Fractions: $\pm 1/64$	TRANSFORMER	750319688
6A	12/21	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750319688	SPECIFICATION SHEET 1 OF 1

