


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	6-5 tie(3+4+5, 6+7+8), @20°C	0.066 ohms max.
INDUCTANCE	6-5 tie(3+4+5, 6+7+8), 50kHz, 100mVAC, Ls	85uH ±5%
SATURATION CURRENT	20% rolloff from initial	6.5A


PART MUST INSERT FULLY TO SURFACE A IN RECOMMENDED GRID




ALTERNATE MARKING DETAIL

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.



Customer to tie terminals 3&4&5 and 6&7&8 on PCB.



Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-0820 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.001 [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750342278
6B	12/18			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750342278	SPECIFICATION SHEET 1 OF 1
6A	4/14	SEE REVISION SHEET FOR REVISION LEVEL				